

## TE Type K - Surface sensor

with wider sensor tip



### Application:

The waterproof and robust surface sensor is versatile. With a stable sensor tube and wider measuring tip, it is suitable for temperature measurements on flat surfaces.

### Execution:

- Sensor type: TE Type K
- Measuring range: -60 to +400°C
- Accuracy: Class 2 in accordance with EN 60584-2
- Response time: 30 s
- Length/diameter of probe/sensor tube: 115 mm/5 mm
- Length/diameter of probe/sensor tube tip: 52 mm/6 mm
- Product/housing material: ABS/TPE/PUR



<b>Art. no.</b>	<b>46108 105</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0602 1993
<b>Sensor type</b>	TE type K
<b>Probe type</b>	Surface probe
<b>Min./max. temperature measuring range</b>	-60 to 400 °C
<b>Accuracy temperature</b>	Class 2 according to EN 60584-2
<b>Response time sensor</b>	30 s
<b>Diameter probe tube</b>	5 mm
<b>Diameter sensor tube tip</b>	6 mm
<b>Length sensor tube</b>	115 mm
<b>Length sensor tube tip</b>	52 mm
<b>Cable length</b>	1.16 m
<b>EN standard</b>	60584-1
<b>Material of housing</b>	ABS/TPE/PUR
<b>Gross Weight</b>	0.147 kg
<b>Product Group</b>	4CF

### EAN

4029547003523