SIEMENS

Data sheet 5TT5800-2



Figure similar

INSTA CONTACTOR WITH 2 MAKE CONTACTS CONTACT FOR 230, 400 V AC, 20 A TRIGGERING 24 V AC

Model		
product brand name		SENTRON
Product designation		Insta contactors
Protection class		
Protection class IP		IP20
Switching capacity		
Switching capacity active power / with filament lamp load	W	1 000
Dissipation		
Active power loss		
• for rated value of the current / with AC / in hot operating state / per pole	W	1.7
Main circuit		
Operating voltage / Rated value		
• minimum	V	250
• maximum	V	250
Operating current / Rated value	A	20
Control current		
Control supply voltage / Rated value	V	24
• maximum	V	24
Product details		
Product component / Slide for manual operation		No

Changes preserved
© Copyright Siemens AG

Product expansion / can be installed / supplementary devices		Yes

Number

Number of NC contacts		0
Number of NO contacts		2

Mechanical Design

Height	mm	90
Width	mm	18
Depth	mm	71
Installation depth	mm	64
Number of width units		1

Certificates

Equipment marking / acc. to DIN EN 61346-2		Q

General Product Approval				Declaration of Conformity	other
CCC	GOST	EAC	other	CE EG-Konf.	Environmental Confirmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)
https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5TT58002


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
http://support.automation.siemens.com/WW/view/en/5TT58002/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT58002

CAx-Online-Generator
http://www.siemens.com/cax

Tender specifications
http://ausschreibungstexte.siemens.com/tiplv

Changes preserved
© Copyright Siemens AG



last modified: 11.03.2015

Changes preserved
© Copyright Siemens AG