

Q - MAX PUNCHES METRIC

| PUNCH SIZE | BOLT SIZE | |
|-------------------|------------------|--|
| 10mm | 6 m/m x 40 | |
| 11mm | 6 m/m x 40 | |
| 12.7mm | 8 m/m x 40 | |
| 14mm | 8 m/m x 40 | |
| 15mm | 8 m/m x 30 | |
| 16mm | 8 m/m x 30 | |
| 17.5mm | 8 m/m x 30 | |
| 18.6mm | 10 m/m x 35 | |
| 19mm | 10 m/m x 35 | |
| 20mm | 10 m/m x 35 | |
| 20.4mm | 10 m/m x 35 | |
| 21mm | 10 m/m x 35 | |
| 22.5mm | 10 m/m x 45 | |
| 24mm | 10 m/m x 45 | |
| 25mm | 10 m/m x 45 | |
| 27.5mm | 10 m/m x 45 | |
| 28.3mm | 10 m/m x 45 | |
| 29mm | 10 m/m x 45 | |
| 30mm | 10 m/m x 45 | |
| 31mm | 10 m/m x 45 | |
| 32.5mm | 12 m/m x 45 | |
| 34mm | 12 m/m x 45 | |
| 35mm | 12 m/m x 45 | |
| 37mm | 12 m/m x 50 | |
| 37.5mm | 12 m/m x 50 | |
| 40mm | 12 m/m x 50 | |
| 45mm | 12 m/m x 50 | |
| 47mm | 12 m/m x 50 | |
| 48mm | 12 m/m x 50 | |
| 50mm | 12 m/m x 50 | |
| 51mm | 12 m/m x 50 | |
| 52mm | 16 m/m x 60 | |
| 54mm | 16 m/m x 60 | |
| 55mm | 16 m/m x 60 | |
| 60mm | 16 m/m x 60 | |
| 64mm | 16 m/m x 65 | |
| 65mm | 16 m/m x 65 | |
| 70mm | 16 m/m x 65 | |
| 75mm | 16 m/m x 65 | |
| 76.5mm | 16 m/m x 70 | |
| 80mm | 16 m/m x 70 | |
| | | |
| | | |
| | | |

