



TrueForce LED Public (Road – SON)



TrueForce LED Road 40-25W E27 730

Philips LED Road lamps are an easy LED solution with a short payback period to replace High Intensity Discharge (HID) and High Pressure Sodium (SON) lamps. TrueForce LED solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce LED road lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast or reflector.

Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions.

Product data


General information		Color Rendering Index (Nom)		Operating and electrical	
Cap-Base	E27 [E27]		70	Input Frequency	50 Hz
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %	Power (Nom)	25 W
Nominal Lifetime (Nom)	50000 h			Lamp Current (Nom)	800 mA
Switching Cycle	50000X			Wattage Equivalent	50 W
Technical Type	25-50W			Starting Time (Nom)	0.5 s
Flux measurement reference	Sphere			Warm Up Time to 60% Light (Nom)	0.5 s
				Power Factor (Nom)	0.9
				Voltage (Nom)	50-60 V
Light technical					
Color Code	730 [CCT of 3000K]				
Luminous Flux (Nom)	4000 lm				
Color Designation	White (WH)				
Correlated Color Temperature (Nom)	3000 K				
Luminous Efficacy (rated) (Nom)	160.00 lm/W				
Color Consistency	<6				

TrueForce LED Public (Road – SON)

Temperature	
T-Case Maximum (Nom)	95 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	Others
Approval and application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	25 kWh

EPREL Registration Number	403601
Product data	
Full product code	871869963251900
Order product name	TrueForce LED Road 40–25W E27 730
EAN/UPC - Product	8718699632519
Order code	929001999402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001999402
Net Weight (Piece)	0.232 kg


Dimensional drawing




TrueForce LED Road 40–25W E27 730

Product	D	C
TrueForce LED Road 40–25W E27 730	61 mm	200 mm

Photometric data



Trueforce LED E27 730




Page 11

Trueforce LED E27 730


TrueForce LED Public (Road – SON)

Photometric data




Trueforce LED E27

Lifetime



Trueforce LED E27



Trueforce LED E27

