

Canvas Select Plus microSD

kingston.com/flash

Powerful performance, speed, and durability

Kingston's Canvas Select Plus microSD is compatible with Android devices and designed with A1 rated performance. It offers improved speed and capacity for loading apps faster and capturing images and videos in multiple capacities up to 512GB¹. Powerful in performance, speed, and durability, the Canvas Select Plus microSD is designed for reliability when shooting and developing high-resolution photos or filming and editing full HD videos. Kingston Canvas cards are tested to be durable in the harshest environments and conditions so you can take them anywhere with confidence that your photos, videos, and files will be protected. Available with a lifetime warranty.

- › Class 10 UHS-I speeds up to 100MB/s²
- › Optimized for use with Android devices
- › Capacities up to 512GB¹
- › Durable
- › Lifetime Warranty



Features/specs on reverse >>



Canvas Select Plus microSD

FEATURES/ BENEFITS

- > **Faster speeds** — Class 10 UHS-I speeds up to 100MB/s.²
- > **Optimized for use with Android devices** — Improved performance when used with an Android smartphone or tablet.
- > **Multiple capacities** — Up to 512GB¹ to store all your memorable photos and videos.
- > **Durable** — For your peace of mind, the card has been extensively tested and proven to be waterproof, temperature proof, shock and vibration proof and X-ray proof.³

SPECIFICATIONS

- > **Capacities**¹ 16GB, 32GB, 64GB, 128GB, 256GB, 512GB
- > **Performance**² 100MB/s Read (16GB-128GB)
100/85MB/s Read/Write (256GB-512GB)
- > **Dimensions** 11mm x 15mm x 1mm (microSD)
24mm x 32mm x 2.1mm (with SD adapter)
- > **Format** FAT32 (16GB-32GB), exFAT (64GB-512GB)
- > **Operating temperature** -25°C~85°C
- > **Storage temperature** -40°C~85°C
- > **Voltage** 3.3V
- > **Warranty/Support** Lifetime



PART NUMBERS

Card (SD adapter included):

- SDCS2/16GB
- SDCS2/32GB
- SDCS2/64GB
- SDCS2/128GB
- SDCS2/256GB
- SDCS2/512GB

Card (SD adapter not included):

- SDCS2/16GBSP
- SDCS2/32GBSP
- SDCS2/64GBSP
- SDCS2/128GBSP
- SDCS2/256GBSP
- SDCS2/512GBSP

Multi-packs of 2 and 3 cards (1 SD adapter included):

- SDCS2/16GB-2P1A
- SDCS2/16GB-3P1A
- SDCS2/32GB-2P1A
- SDCS2/32GB-3P1A
- SDCS2/64GB-2P1A
- SDCS2/64GB-3P1A

1. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/flashguide.

2. Speed may vary due to host hardware, software, and usage.

3. IEC/EN 60529 IPX7 certified for protection against continual water submersion up to 30 minutes at a depth up to 1m. Withstands temperature range from -25 °C to 85 °C. Based on MIL-STD-883H, METHOD 2002.5 military standard test method. Protected against X-ray exposure based on ISO7816-1 guidelines.

