



Synergy 21 LED Subordinate Bodeneinbaustrahler 9W RGB+CCT mit Funk und WLAN *Milight/Miboxer*



kwh/1000h:	9,00
Lumen:	700
Watt:	9,0
Nennlebensdauer:	35000 Std.
Schaltzyklen:	50000
Opt. Umgebungstemp.:	25 °C



Product Name: 9W RGB+CCT LED Underground Light
(Subordinate Lamp)
Model No.: SYS-RD2
Input Voltage: DC24V
Power: 9W
Working Temperature: -20~60°
Color temperature: 2700~6500K
Luminous Flux: 700LM
Light Efficiency: 80LM/W
CRI: >80
Lifespan: 50000h
Beam Angle: 15°
IP Rate: IP68
size: 150*138*104mm

Energieeffizienzklasse: A
kWh/1000h: 9


Merkmale

Merkmal	Wert
Abstrahlwinkel:	15

Merkmal	Wert
CC oder CV:	CV
CRI:	80
Dimmbar:	Ja
EPREL_ANTI_GLARE_SHIELD:	false
EPREL_BEAM_ANGLE:	15
EPREL_BEAM_ANGLE_CORRESPONDENCE:	NARROW_CONE_90
EPREL_CAP_TYPE:	Others
EPREL_CHROMATICITY_COORD_X:	0.313
EPREL_CHROMATICITY_COORD_Y:	0.337
EPREL_CLAIM_EQUIVALENT_POWER:	false
EPREL_COLOUR_RENDERING_INDEX:	80
EPREL_COLOUR_TUNEABLE_LIGHT_SOURCE:	false
EPREL_CONNECTED_LIGHT_SOURCE:	true
EPREL_CORRELATED_COLOUR_TEMP:	2700,6500
EPREL_CORRELATED_COLOUR_TEMP_TYPE:	RANGE
EPREL_DIMENSION_DEPTH:	104
EPREL_DIMENSION_HEIGHT:	150
EPREL_DIMENSION_WIDTH:	138
EPREL_DIMMABLE:	YES
EPREL_DIRECTIONAL:	DLS
EPREL_ENERGY_CLASS:	E
EPREL_ENERGY_CONS_ON_MODE:	9
EPREL_FLICKER_METRIC:	0.6
EPREL_HIGH_LUMINANCE_LIGHT_SOURCE:	false
EPREL_LIGHTING_TECHNOLOGY:	LED
EPREL_LUMEN_MAINTENANCE_FACTOR:	0.55
EPREL_LUMINOUS_FLUX:	600
EPREL_MAINS:	NMLS
EPREL_MAX_COLOUR_RENDERING_INDEX:	92
EPREL_MIN_COLOUR_RENDERING_INDEX:	80
EPREL_ON_MARKET_END_DATE:	01/01/2031


Merkmal	Wert
EPREL_ON_MARKET_START_DATE:	01/01/2020
EPREL_POWER_ON_MODE:	6.4
EPREL_POWER_STANDBY:	0.40
EPREL_POWER_STANDBY_NETWORKED:	0.40
EPREL_R9_COLOUR_RENDERING_INDEX:	9
EPREL_REGISTRANT_NATURE:	MANUFACTURER
EPREL_STROBOSCOPIC_EFFECT_METRIC:	0.5
EPREL_SURVIVAL_FACTOR:	0.55
Grösse:	150*138*104
Lichtfarbe:	RGB-WW
Lichtfarbe in Kelvin:	2700~6500
Lumen:	700
Schutzklasse:	IP68
Volt:	24
Gewicht:	1 Kg
Garantie:	24.00 Monate

Weitere Bilder



Brightness adjustable & Color temperature adjustable

Brightness adjustable, Adjust the color temperature from 2700-6500K, make the light you want



Stainless steel surface ring

High quality stainless steel materials; not easy to fade and sunproof



Stalinite mask

Made of high quality stalinite, High hardness, nonbreakable and high light-transmittance





Optical Lens

Anti-dazzling optical lens; diverging light scientifically. Symmetrical and bright light ray



PC built-in fitting

Pressure and corrosion resistance, not easy to deformation, easy installation



End cap screw

Stainless steel material. Waterproof and dustproof



Integrated convection heat dissipation

Convection design, better heat dissipation, safe and stable

COMPATIBLE REMOTE SHEET

Product	Compatible Remote

Zubehör

Art.-Nr.	Name
158699	Synergy 21 LED Subordinate Garten Lampe 15W RGB+CCT mit Funk und WLAN IP65 24V Milight/Miboxer*
158700	Synergy 21 LED Subordinate Garten Lampe 9W RGB+CCT mit Funk und WLAN IP65 24V *Milight/Miboxer*
158702	Synergy 21 LED Subordinate Poolleuchte 12W RGB+CCT mit Funk und WLAN *Milight/Miboxer*
158703	Synergy 21 LED Subordinate Wandfluter 24W RGB+CCT IP66 24V *Milight/Miboxer*

Art.-Nr.	Name
158704	Synergy 21 LED Subordinate Controller 1-Channel Amplifier *Milight/Miboxer*
158705	Synergy 21 LED Subordinate Controller 1-Channel Host *Milight/Miboxer*
158962	Synergy 21 LED Subordinate Kabel/Stecker SYS Serie *Milight/Miboxer*
158963	Synergy 21 LED Subordinate Kabel/Stecker SYS Serie *Milight/Miboxer*
158964	Synergy 21 LED Subordinate Kabel/Stecker SYS Serie *Milight/Miboxer*
158965	Synergy 21 LED Subordinate Kabel/Stecker SYS Serie *Milight/Miboxer*