

MNX PC 175/75 HG



Sample photo

Order symbol: PC 175/75 HG
Product nbr: 6011320
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074024411
EI. number:
 Finland: 3422252
 Electric No. Denmark: 8212022645
 Electric No. Italy: 7351113
 Electric No. Sweden: 2535564

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Length	Width	Height	Accessories:			
mm:	180	180	75			MIN 15	DIN-15 Mounting rail		
inch:	7.1	7.1	3.0			MIV 15	DIN-35 Mounting rail		
Materials:									
Material:	Polycarbonate						FP A 175/180	Front plate (Aluminium)	
Base colour:	RAL 7035 -light grey						HFP 180	Front plate hinge series	
Cover screws material:	Polyamide						FP 22046	Wall fastening lug (4 pcs)	
Cover colour:	RAL 7035 -light grey						Rating:		
Cover screws colour:	Grey						Ingress Protection (EN 60529): IP66/IP67		
Gasket material:	TPE						Impact Resistance (EN 62262): IK08		
Temperatures:								Electrical insulation: Totally insulated	
Temperature °C (short term):	-40 ... 120 °C						Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °C (continuous):	-40 ... 80 °C						UV resistance: UL 508		
Temperature °F (short term):	-40 ... 250 °F						Flammability Rating: UL 746C 5"		
Temperature °F (continuous):	-40 ... 175 °F						Glow Wire Test (IEC 695-2-1) °C: 960		
Accessories:								NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
MIV 175	Mounting plate (Galvanized steel)						Certificates:		
								Germanischer Lloyd (GL)	
								SGS Fimko	
								Gost R	

