

PDJN clamp holder, negative, left

For copy turning and longitudinal turning using DN indexable insert

ATORN[®]

Application


For copy turning and longitudinal turning using DN indexable insert 55°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type D, 93° pitch angle, 55° tip angle, 0° clearance angle

Advantage

- very slim geometry, optimised for contour turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



Art. No.	17838 066
ISO name	PDJN R/L 3232 P15
Shaft height	32 mm
Shank width	32 mm
Length	170 mm
Length of head	34 mm
Programming size	40 mm
Suitable for indexable inserts	DN.. 1506..
Tool design	Left
DIN	4983

EAN-Code

4050293348026