

Plug socket module Germany w. LED (VDE)



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	With LED display Termination at the rear

Version

Termination method	Screw termination
Field of application	Germany (VDE)

Termination data

Supply voltage	250 V AC
Nominal current	16 A
Nominal frequency	50 Hz

Technical characteristics

Conductor cross-section	6 mm ²
Mounting depth	62 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	0.333 g
Country of origin	Belgium
European customs tariff number	85366990
GTIN	5713140154872
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406