

## Hammer drill GBH 2-26 F/SDS-plus

830 W

**BOSCH**

### Application:

For drilling and chiselling with pneumatic striking tools in stone and concrete

### Execution:

- overload coupling
- Variable rotation speed

### Advantage:

- clutch claws unlock and torque is minimised to prevent the tool blocking abruptly

### Delivery:

In case



<b>Art. no.</b>	<b>70170 044</b>
<b>Brand</b>	BOSCH
<b>Manufacturer Part Number</b>	06112A4000
<b>Model</b>	GBH 2-26 F / SDS-plus
<b>Manufacturer Article Number</b>	06112A4000
<b>Battery included</b>	No
<b>Max. impact energy</b>	2.7 J
<b>Max. impact rate</b>	4000 rpm
<b>Min./max. impact rate</b>	0-4000 rpm
<b>Power input</b>	830 W
<b>Max. drilling diameter in concrete</b>	26 mm
<b>Max. drilling diameter in wood</b>	30 mm
<b>Max. drilling diameter in steel</b>	13 mm
<b>Max. drilling diameter in masonry</b>	68 mm
<b>Tool holding device</b>	Drill chuck Auto-Lock
<b>Idle speed 1st gear min./max.</b>	0-900 rpm
<b>Weight</b>	2.9 kg
<b>With speed control</b>	Yes
<b>With rubber-coated handle</b>	Yes
<b>With chisel function</b>	Yes
<b>Gross Weight</b>	5.550 kg
<b>Product Group</b>	731

### EAN

3165140859202