



Tool Kits

K I T S

| Product code | EAN code | Dimensions mm/inch | Description | | |
|--------------|----------|---------------------------|-----------------------|-------|---|
| 9850 | 0111343 | 490x390x120/19.6x15.6x4.8 | Lindstrom Tool Kit* | 13500 | 1 |
| 9851 | 0111411 | 490x390x120/19.6x15.6x4.8 | Lindstrom Tool Kit* * | 13500 | 1 |

NEW

**9850
9851**

Contents

| | | | |
|-----------|---------------------------------------|--------------|--------------------------------------|
| 8070 | Adjustable/6.0 | 2047PR-1-2 | Double offset PH 1 and 2 |
| 9072P | Reversible/10.0 | 2744 | Multi Purpose Shear |
| 2628-180 | Combination pliers/7.2 | 479-08 | Claw hammer |
| 2430G-160 | Snipe nose pliers/6.4 | TL 7314 SA | Tweezers, general purpose (serrated) |
| 2128G-160 | Side cutters/6.4 | TL 475 SA | Tweezers, fine pointed |
| 2223D-150 | Wire strippers/6.0 | BE-9770 | Hexagon socket set |
| 8140 | Electronic side cutters small | 5515L | Small mirror |
| 8160 | Electronic side cutters medium | 2509 | Flexible pick-up tool |
| 7890 | Electronic side cutters short | 8045LVDE | Voltage tester |
| 7291 | Electronic end cutter | 5552 | Trimming knife |
| 208 | Mini hacksaw | 1-473-08-2-2 | File set |
| 268 | Junior hacksaw | 2-470-14-2-0 | Needle file set |
| BE-8220 | Screwdrivers 3.0 mm/0.11 (long blade) | 1933M/6T | Small double open-end spanner set |
| BE-8040 | Screwdrivers 4.0 mm/0.15 | 2800N | Small cable cutters |
| BE-8150 | Screwdrivers 5.5 mm/0.21 | | Tap measure 3 m |
| BE-8155 | Screwdrivers 6.5 mm/0.26 | | Cutting knife |
| BE-8800 | PZ 0 | | Soldering iron |
| BE-8810 | PZ 1 | | De-soldering disp. |
| BE-8820 | PZ 2 | | Tool box |
| 7200/S7 | Precision screwdriver set | | |
| * | Euro plug | | |
| ** | U.K. plug | | |



| Product code | EAN code | Dimensions mm/inch | Description | | |
|--------------|----------|-------------------------|-------------|------|---|
| 9852 | 0114092 | 40x310x220/1.6x12.4x8.8 | | 1985 | 1 |

NEW

9852

Contents

| | | | |
|-----------|--|-----------|--------------------------------------|
| 8070 | Adjustable wrench 155 mm/6.0 | 8045 LVDE | Voltage tester 150-250 V |
| 2421G-160 | Flat nose pliers 160 mm/6.4 | 8160 | Side cutter 125 mm/5.0 |
| 2101G-160 | Side cutter 160 mm/6.4 | 7890 | Snipe nose plier 132 mm/5.3 |
| 2628G-180 | Combination pliers 180 mm/7.2 | TL AA-SA | Tweezer, strong fine tips 130 mm/5.2 |
| BE-8210 | Slotted screwdriver 0.4x2.5 mm/0.01x0.09 | TL K-AP | Knife |
| BE-8040 | Slotted screwdriver 0.8x4.0 mm/0.03x0.15 | TM3M | Tape measure |
| BE-8150 | Slotted screwdriver 1.0x5.5 mm/0.04x0.21 | | |
| BE-8155 | Slotted screwdriver 1.2x6.5 mm/0.05x0.26 | | |
| BE-8600 | Phillips® screwdriver PH 0 | | |
| BE-8610 | Phillips® screwdriver PH 1 | | |
| BE-8620 | Phillips® screwdriver PH 2 | | |

