



LABELING SET FOR MOBILE PANEL 277 AMOUNT: SEE TECHNICAL DATA

Product type designation	
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	50 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	90 %
Films	
Number of films per sheet	6
printable with laser printer	Yes
Dimensions	
Width	210 mm
Height	297 mm
Scope of supply	

Delivery unit in items	2; 2 sheets with 3 labeling strips each, incl. corner seals, O-ring, replacement screw, decorative film for corner seal
Number of sets	6
other	
Note:	For Mobile Panel 277
Usable in the following products	
• Product 1	6AV6645-0CA01-0AX0
• Product 2	6AV6645-0CB01-0AX0
• Product 3	6AV6645-0CC01-0AX0
• Product 4	6AV6645-0BE02-0AX0
last modified:	12.03.2015