

Radial tool holder shape B4 overhead left-hand, short

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground

Art. no.	22778 052
Brand	ORION
Manufacturer Part Number	22778052
VDI mount diameter	25 mm
Form	B4 L overhead
Height	16 mm
Width	55 mm
Holder width	30 mm
Width 2	7 mm
Height 2	25 mm
Height 3	30 mm
Holder support length	16 mm
Length	30 mm
DIN	69880-1
Gross Weight	0.900 kg
Product Group	2AC



EAN

405362546466 1