


PXMBN12CAF Datasheet

Product Name // M12 Series Brass Nickel Plated Female Sealing Cap

[View Product Page](#)


// Product Description:

- ⊕ M12 Series Sealing Caps
- ⊕ Can be used to maintain IP rating of unmated connectors
- ⊕ Compatible with all M12 Series Connectors and M Series Power Distribution Unit inputs
- ⊕ Choice of material to suit connector being capped
- ⊕ Choice of Male or Female to suit connector being capped

// General Information:

| | |
|---------------------------------|--------------------------------|
| Product Display Title: | M12 Series Sealing Caps |
| Product Family: | Circular Automation Connectors |
| Product Series: | M12 Series |
| Weight: | 0.015 |
| Body Material: | Brass - Nickel Plated |
| Contact Type: | Socket Contact |
| Coupling Type: | Screw |
| Diameter Over Coupling Ring Mm: | 14.5mm |
| Function: | Sealing Cap |
| Ip Rating: | IP67 |
| Max Operating Temperature: | +80°C |
| Min Operating Temperature: | -25°C |
| Pin Layout Code: | X Code |
| Rohs Compliant: | Yes |
| Thread Size: | M12 x 1 |

// Product PDF Links

[M12 Series automation connectors...](#)

// Product 3D CAD Model Links

[PXMBN12CAF3D CAD Model](#)