

Pneumatic spiral hose

Made of polyurethane (PU)



Application:

For connection to compressed-air tools and compressed-air machines.

Execution:

- With rotating brass connection parts
- With straight input and output piece (10 and 50 cm)
- Resistant to oil, petrol and acid

Advantage:

- Perfect in combination with spring balances



Art. no.	75051 110
Brand	RED ROOSTER
Manufacturer Part Number	PT-02525SJ
Hose length	5 m
Outer diameter of hose	9.5 mm
Inner hose diameter	6.5 mm
Connection thread	G 1/4 inch
Max. operating pressure	10 bar
Min./max. temperature conditions	-20 to 80 °C
Gross Weight	0.452 kg
Product Group	7AF

EAN

8717981146031