

Angular milling cutter HSSE Co 5

ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery



Art. no.	15815 130
Brand	ORION
Manufacturer Part Number	15815130
Cutting material	HSSE Co5
Type	N
Number of cutting edges	10 PCS
Chamfer angle	60 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	20 mm
Width of cutting edge	8 mm
Immersion depth	18 mm
Length	63 mm
Shank diameter	12 mm
Form	D
fz steel 700	0.05 mm
Gross Weight	0.025 kg
Product Group	106

EAN

4039247098200