

## Pneumatic rod grinder RRG-2690

Angled version



### Application:

for deburring, finishing welding and cast seams as well as other light grinding work

### Advantage:

- Movable air connection guarantees easy mobility of the grinder
- The tool performance can be adjusted via the adjustment wheel if desired by the operator



<b>Art. no.</b>	<b>75066 054</b>
<b>Brand</b>	RED ROOSTER
<b>Manufacturer Part Number</b>	RRG-2690
<b>Model</b>	RRG-2690
<b>Design</b>	Offset
<b>Valve design</b>	Lever valve
<b>Max. idle speed</b>	20000 rpm
<b>Power output</b>	260 W
<b>Air consumption</b>	7.5 l/s
<b>Connection thread</b>	1/4 inch
<b>Sound-pressure level</b>	84 dB
<b>Inner hose diameter</b>	10 mm
<b>Length</b>	166 mm
<b>Max. clamping diameter</b>	6 mm
<b>Collet chuck diameter</b>	6 mm
<b>Suitable for max. sanding block diameter</b>	35 mm
<b>Weight</b>	0.6 kg
<b>Gross Weight</b>	0.640 kg
<b>Product Group</b>	7AE

### EAN

8717981400102