



## SOCKET & RELAY MODULES

### 18FF-4Z-C7 DIN Rail Socket





Socket Characteristics	
Ambient Temperature	-40°C to +70°C
Voltage Rating	250VAC
Current Rating	7A (per pole)
DIN Protection rating	IP20 (DIN40050)
Construction material	PA66+GF VO (UL)
Spring Contact material	QSn6.5-0.1
Retainer	18FF-KRC
White plastic tag	Supplied with socket
Modules	Non - available
Terminal torque	0.6Nm
Wire strip length	7mm
Relay Applications	HF18FF (4 Poles)
Dielectric Strength	2000VAC
Max. wire range	2 x 1.5mm <sup>2</sup>

### Dimensions, Socket Layout and Wiring Diagram


(Units in mm)

#### Outline Dimensions



(Top View)

#### Wiring Diagram



(Top View)