

## Product information

# 97 53 19

### KNIPEX Twistor® T

Self-Adjusting Crimping Pliers for wire ferrules  
With rotatable die head



- Crimp head can be rotated 360°, with 8 locking positions
- Trapezial crimp profile, high capacity range from 0.14 to 10 mm<sup>2</sup>
- Wire ferrules can be crimped from almost any working position
- Crimping pliers adjust automatically to different cross-sections
- Crimp opening accessible from both sides, a length of up to 18 mm can be crimped in one operation, extra-long wire ferrules can be fed in
- Crimping of Twin wire ferrules up to 2 x 6 mm<sup>2</sup> possible
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Light and handy tool, manual force reinforced by toggle lever mechanism
- Special quality chrome vanadium electric steel, oil-hardened



#### General

Article No.	97 53 19
EAN	4003773088097
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	486 g
Dimensions	200 x 80 x 26 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

#### Technical details

Application	Wire ferrules
Capacity in square millimetres	0.14 — 10 mm <sup>2</sup>
AWG	26 — 8
Number of crimping positions	1

*technical change and errors excepted*







