

## LED workplace light Highlight

With and without dimmer



### Execution:

- LED module with very low power consumption
- Streamlined shape, for universal use
- High-performance chip with lamp life of min. 50,000 operating hours
- Protected against splash water and dust, with power supply unit
- Glare- and flicker-free light, low-reflection, 160-degree uniform illumination
- 400-lumen light output, colour temperature: daylight white, approx. 5500 Kelvin
- Rubber-coated 66-mm magnetic base with adhesive force of 180 N
- Lamp head 90 x 30 x 13 mm, total length 620 mm
- Ref. no. 150: No dimmer
- Ref. no. 152: With dimmer (continuously variable)

### Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



<b>Art. no.</b>	<b>56879 152</b>
<b>Brand</b>	BAUER & BÖCKER
<b>Manufacturer Part Number</b>	900/42D
<b>Power rating</b>	2.5 W
<b>Arm length</b>	551 mm
<b>IP protection class</b>	IP 65
<b>Dimmable</b>	Yes
<b>Gross Weight</b>	0.900 kg
<b>Product Group</b>	5ID

### EAN

4260131238062