

## Pneumatic spiral hose

Made of polyamide



### Application:

For connection to compressed-air tools and compressed-air machines.

### Execution:

- With special fitting connections at both ends
- Suitable for water and air
- Max. pressure: 10 bar
- Max. temperature: 90°C
- For a clearly organised workplace
- For reducing the risk of accidents



<b>Art. no.</b>	<b>75052 045</b>
<b>Brand</b>	PREVOST
<b>Manufacturer Part Number</b>	SPIC 85
<b>Hose length</b>	5 m
<b>Outer diameter of hose</b>	10 mm
<b>Inner hose diameter</b>	8 mm
<b>Connection thread</b>	G 1/4 inch
<b>Max. operating pressure</b>	10 bar
<b>Gross Weight</b>	0.338 kg
<b>Product Group</b>	758

### EAN

3660058027984