





Product Details			
Model Name	LP	ECCO Group Europe Part Number	30102270
Internal ERP Description	BEACON, LP, XEN, 2W, MV, AMBER		
Product Type	Xenon Beacon	Application	Automotive / Industrial
Product Image – Amber beacon only shown		Product Dimensions	
			

Electrical Characteristics			
Input Voltage	10-100V DC, 20-72V AC	Input current	300mA @ 12V DC, 120mA @ 24V DC 77mA @ 48V DC, 66mA @ 60V DC 270mA @ 30V AC, 110mA @ 60V AC
Frequency	75 FPM	Light Source	Non-replaceable
Flash Mode	Single flash	Flash Pattern	N/A
Technology	Xenon	Power rating	2 W
		Estimated Tube Life	3,000 Hours
Other features	Reverse polarity protection		

Photometric Characteristics			
Colour	Amber	Polar Plot	
Max intensity at HV0	26 cd from top		
Min intensity	4 cd from side		
Timing Diagram			
			

Enclosure			
IP rating	IP 67	Fixing centres	45 mm
Cable exit	Central base grommet	Fastening hardware	2 x M5 x 14mm studs with M5 nuts
Cable dimensions	2 x 0.75mm ²	Packaging	Thin wall carton
Recommended Mounting	Upright or 90°	Max Fastening Torque	3 N/m
Weight (unboxed)	130g	Weight (boxed)	150g

Approvals and Certifications			
EMC	UN ECE R10-03 6101	WEEE	Yes (marking only for own brand products)
CE	Yes	RoHS	Yes