



Identification	Part number	Drawing	Dimensions in mm
<p>Fibre optic cable, PushPull V4 – SC duplex, single mode overmoulded</p> <p>Length: a = 1 m</p> <p>a = 2 m</p> <p>a = 3 m</p> <p>a = 4 m</p> <p>a = 5 m</p> <p>a = 6 m</p> <p>a = 7 m</p> <p>a = 8 m</p> <p>a = 9 m</p> <p>a = 10 m</p> <p>a = 11 m</p> <p>a = 12 m</p> <p>a = 13 m</p> <p>a = 14 m</p> <p>a = 15 m</p> <p>a = 20 m</p> <p>a = 25 m</p> <p>a = 30 m</p> <p>a = 35 m</p> <p>a = 40 m</p> <p>a = 45 m</p> <p>a = 50 m</p> <p>a = 60 m</p> <p>a = 70 m</p> <p>a = 80 m</p> <p>a = 90 m</p> <p>a = 100 m</p>	<p>33 61 431 0010 004</p> <p>33 61 431 0020 004</p> <p>33 61 431 0030 004</p> <p>33 61 431 0040 004</p> <p>33 61 431 0050 004</p> <p>33 61 431 0060 004</p> <p>33 61 431 0070 004</p> <p>33 61 431 0080 004</p> <p>33 61 431 0090 004</p> <p>33 61 431 0100 004</p> <p>33 61 431 0110 004</p> <p>33 61 431 0120 004</p> <p>33 61 431 0130 004</p> <p>33 61 431 0140 004</p> <p>33 61 431 0150 004</p> <p>33 61 431 0200 004</p> <p>33 61 431 0250 004</p> <p>33 61 431 0300 004</p> <p>33 61 431 0350 004</p> <p>33 61 431 0400 004</p> <p>33 61 431 0450 004</p> <p>33 61 431 0500 004</p> <p>33 61 431 0600 004</p> <p>33 61 431 0700 004</p> <p>33 61 431 0800 004</p> <p>33 61 431 0900 004</p> <p>33 61 431 1000 004</p>	<p>a = length</p>	
<p>Fibre optic breakout cable, single mode</p> <p>Length: 10 m</p> <p>Length: 20 m</p> <p>Length: 100 m</p>	<p>33 58 751 0100 002</p> <p>33 58 751 0200 002</p> <p>33 58 751 1000 002</p>	<p>PUR jacket 2-fibre single mode Outer diameter: 6.5 mm Min. bending radius: 10.4 cm Installation: 10.4 cm Operating: 5.2 cm</p>	

Other cable lengths on request