


PELTIER-ELEMENTE

Einstufige Standard Module

Soweit die Produktbezeichnungen grün dargestellt sind handelt es sich um Lagertypen.



Bezeichnung	Konfektionierung	U _{max} V	Q _{cmax} W	I _{max} A	ΔT _{max} K	Warme Seite	Kalte Seite
QC-06-004-15		0,5	0,32	1,3	73	4mm x 4mm	2mm x 4mm
QC-7-1.4-3.7M		0,9	1,90	3,7	73	12mm x 12mm	12mm x 12mm
QC-7-1.4-6.0M		0,9	2,90	6,0	72	12mm x 12mm	12mm x 12mm
QC-7-1.4-8.5M		0,9	3,90	8,5	71	12mm x 12mm	12mm x 12mm
QC-17-1.0-2.5M		2,1	3,00	2,5	70	12mm x 12mm	12mm x 12mm
QC-17-1.0-3.0M		2,1	3,50	3,0	72	12mm x 12mm	12mm x 12mm
QC-17-1.0-3.9M		2,1	4,60	3,9	71	12mm x 12mm	12mm x 12mm
QC-17-1.4-3.7MS	Silikondichtung	2,1	4,60	3,7	68	15mm x 15mm	15mm x 15mm
QC-17-1.4-6.0M		2,1	7,10	6,0	72	15mm x 15mm	15mm x 15mm
QC-17-1.4-8.5MS	Silikondichtung	2,1	9,30	8,5	68	15mm x 15mm	15mm x 15mm
QC-17-1.4-8.5MS	Silikondichtung	2,1	9,50	8,5	71	15mm x 15mm	15mm x 15mm
QC-18-5.0-60.0M		2,2	72,50	60,0	71	40mm x 40mm	40mm x 40mm
QC-18-5.0-75.0M		2,2	89,00	75,0	71	40mm x 40mm	40mm x 40mm
QC-32-0.6-1.2MS	Silikondichtung	3,9	2,60	1,2	70	8mm x 10mm	8mm x 8mm
QC-31-1.0-2.5M		3,8	5,50	2,5	73	15mm x 15mm	15mm x 15mm
QC-31-1.0-3.0M		3,8	6,50	3,0	72	15mm x 15mm	15mm x 15mm
QC-31-1.0-3.9M		3,8	8,50	3,9	71	15mm x 15mm	15mm x 15mm
QC-31-1.4-3.7M		3,8	8,50	3,7	73	20mm x 20mm	20mm x 20mm
QC-31-1.4-6.0M		3,8	12,90	6,0	71	20mm x 20mm	20mm x 20mm
QC-31-1.4-8.5M		3,8	17,30	8,5	71	20mm x 20mm	20mm x 20mm
QC-32-2.0-9.0M		3,8	19,00	9,0	71	25,4mm x 28,4mm	25,4mm x 25,4mm
QC-32-2.0-15.0M		3,8	31,00	15,0	71	25,4mm x 25,4mm	25,4mm x 25,4mm
QC-35-1.4-3.7M		4,2	9,50	3,7	73	15mm x 30mm	15mm x 30mm
QC-35-1.4-6.0M		4,2	14,60	6,0	72	15mm x 30mm	15mm x 30mm
QC-35-1.4-8.5M		4,2	19,90	8,5	71	15mm x 30mm	15mm x 30mm
QC-63-1.4-6.0M		7,7	26,00	6,0	71	20mm x 40mm	20mm x 40mm
QC-63-1.0-2.5M		7,6	10,90	2,5	73	15mm x 30mm	15mm x 30mm
QC-63-1.0-3.0M		7,6	13,10	3,0	72	15,3mm	15mm x 30mm
QC-63-1.0-3.9M		7,6	16,20	3,9	70	15mm x 30mm	15mm x 30mm
QC-63-1.4-3.7M		7,6	17,10	3,7	73	20mm x 40mm	20mm x 40mm
QC-63-1.4-8.5M		7,6	33,00	8,5	70	20mm x 40mm	20mm x 40mm
QC-70-2.5-24.0		8,5	115,00	24,0	69	36,4mm x 54,4mm	36,4mm x 50,2mm
QC-71-1.0-2.5M		8,6	12,40	2,5	73	22,4mm x 22,4mm	22,4mm x 22,4mm
QC-71-1.0-3.0M		8,6	14,90	3,0	72	22,4mm x 22,4mm	22,4mm x 22,4mm
QC-71-1.0-3.9M		8,6	19,30	3,9	71	22,4mm x 22,4mm	22,4mm x 22,4mm
QC-71-1.4-3.7M		8,6	19,30	3,7	73	30mm x 30mm	30mm x 30mm
QC-71-1.4-6.0M		8,6	29,60	6,0	72	30mm x 30mm	30mm x 30mm
QC-71-1.4-8.5M		8,6	38,00	8,5	70	30mm x 30mm	30mm x 30mm
QC-71-1.6-15.0M		8,6	75,00	15,0	71	29,8mm x 33,8mm	29,8mm x 29,2mm
QC-71-2.0-12.0M		8,6	62,00	12,0	73	40mm x 40mm	40mm x 40mm
QC-71-2.0-15.0M		8,6	74,00	15,0	71	40mm x 40mm	40mm x 40mm
QC-71-1.4-9.0M		9,2	46,00	8,7	74	30mm x 30mm	30mm x 30mm
QC-75-2.5-20.0M		10,0	100,00	20,0	70	37,4mm x 59mm	37,4mm x 54,8mm
QC-127-1.0-2.5M		15,5	22,00	2,5	73	30mm x 30mm	30mm x 30mm
QC-127-1.0-2.5MS	Silikondichtung	15,5	22,00	2,5	70	30mm x 30mm	30mm x 30mm
QC-127-1.0-3.0M		15,5	25,00	3,0	71	30mm x 30mm	30mm x 30mm
QC-127-1.0-3.9M		15,5	33,00	3,9	70	30mm x 30mm	30mm x 30mm
QC-127-1.4-3.7M		15,5	34,50	3,7	73	40mm x 40mm	40mm x 40mm
QC-127-1.4-6.0M		15,5	52,00	6,0	71	40mm x 40mm	40mm x 40mm
QC-127-1.4-6.0MS	Silikondichtung	15,5	52,00	6,0	68	40mm x 40mm	40mm x 40mm
QC-127-1.4-8.5M		15,5	72,00	8,5	71	40mm x 40mm	40mm x 40mm
QC-127-1.4-8.5MD	250mm-AWG-Kabel	15,5	72,00	8,5	71	40mm x 40mm	40mm x 40mm
QC-127-1.6-9.0M		15,5	75,00	9,0	69	56mm x 56mm	56mm x 56mm
QC-127-2.0-12.0M		15,5	88,00	12,0	72	50mm x 54mm	50mm x 50mm
QC-127-2.0-15.0M		15,5	110,00	15,0	71	50mm x 54mm	50mm x 50mm
QC-127-1.4-8.5MS	Silikondichtung	15,5	70,00	8,5	68	40mm x 40mm	40mm x 40mm
QC-127-1.4-3.7MS	Silikondichtung	15,5	33,80	3,7	73	40mm x 40mm	40mm x 40mm
QC-144-1.2-8.0M		19,1	91,40	8,0	71	16,8mm x 76,7mm	16,8mm x 72,4mm
QC-161-1.6-15.0M		19,5	180,00	15,0	69	40mm x 40mm	40mm x 40mm
QC-241-1.0-3.0M		29,5	49,00	3,0	71	40mm x 40mm	40mm x 40mm
QC-241-1.6-15.0M		29,5	200,00	15,0	68	50mm x 50mm	50mm x 50mm
QC-241-1.0-3.9M		29,5	64,00	3,9	71	40mm x 40mm	40mm x 40mm
QC-241-1.4-8.5M		29,4	140,00	8,5	69	54,4mm x 57,0mm	54,4mm x 54,4mm
QC-450-0.8-3.0M		54,8	95,00	3,0	70	54,4mm x 57,0mm	54,4mm x 54,4mm