

ARCA 507030

FIBOX
Enclosing innovations



Sample image

Order symbol: ARCA 507030

Product nbr: 8120031

Description: Cabinet, PC


Remarks: Grey cover. 2-point locking, hinges on the short side

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate, 3mm double bit lock(s) with key, 5 versions with swinghandle 2-point locking system. Door guide included.

EAN: 6418074086006

El. number:

- Finland: 3424062
- Denmark: 8212095384
- Sweden: 2500119



| Dimensions: | Height | Width | Depth |
|-------------|--------|-------|-------|
| mm: | 500 | 700 | 300 |
| inch: | 19.69 | 27.56 | 12.2 |

Materials:

| | |
|------------------|----------------------|
| Material: | Polycarbonate |
| Base colour: | RAL 7035 -light grey |
| Cover colour: | RAL 7035 -light grey |
| Gasket material: | Polyurethane |

Temperatures:

| | |
|------------------------------|-------------|
| Temperature °C (short term): | -40 ... 120 |
| Temperature °C (continuous): | -40 ... 80 |
| Temperature °F (short term): | -40 ... 250 |
| Temperature °F (continuous): | -40 ... 175 |

Accessories:

| | |
|-----------------|---|
| SBK ARCA 50 | Support bar kit (435 x 40 x 30) |
| MPX ARCA 7050 | Mounting plate (630x430 mm) (630 x 430 x 5) |
| PMK ARCA 70 | PoleMounting kit. for pole \varnothing 100-300mm (685 x 485 x 35) |
| RCS ARCA 5070 | Rain canopy set for size 5070 (20 x 700 x 30) |
| DSP ARCA RM | Door stopper ARCA, right. midsize 5070-8060 |
| DRS ARCA 507030 | DIN rail frame set (685 x 485 x 35) |
| IDS ARCA 5070 | Inner door set (485 x 385 x 35) |
| SBK ARCA 70 | Support bar kit (615 x 50 x 30) |
| DSP ARCA LM | Door stopper ARCA, left. midsize 5070-8060 |
| MPS ARCA 7050 | Mounting plate (630x430x2 mm) (630 x 430 x 2) |
| MPMP ARCA 7050 | Mounting plate multiperforated (630x430x2 mm - \varnothing 3.6 mm) (630 x 430 x 2) |
| MPP ARCA 5070 | Mounting plate perforated (630x430x2 mm - 26x11 mm) (430 x 630 x 2) |

Rating:

| | |
|--|--------------------------|
| Ingress protection (EN 60529): | IP66; |
| Impact Resistance (EN 62262): | IK10; |
| Electrical insulation: | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1 |
| UV resistance: | UL 508 |
| Flammability Rating: | UL 94 5VA |
| Glow Wire Test (IEC 695-2-1) °C: | 960 °C |
| NEMA Class | NEMA 1, 4, 4X, 12 and 13 |

Certificates:

Certificate FI 40467