

Product information

97 52 09

Crimping Pliers

For two-hand operation




- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened

General

Article No.	97 52 09
EAN	4003773025498
Pliers	burnished
Head	burnished
Handles	with non-slip plastic grips
Weight	571 g
Dimensions	250 x 78 x 26 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	insulated and non-insulated wire ferrules
Capacity in square millimetres	10 / 16 / 25 mm ²
Number of crimping positions	3
AWG	8 / 6 / 4
AWG	8 / 6 / 4

technical change and errors excepted