

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 120
Brand	AMF
Manufacturer Part Number	80812
DIN	787
Thread dimension	M8
Groove width	8 mm
Length excluding head	50 mm
Outer diameter	7.7 mm
Thread length	35 mm
Length of head	13 mm
Head height	6 mm
Gross Weight	0.041 kg
Product Group	260

EAN

4020772080815