



FT50-C Fiberglass Insulated Tubing

FT50-C

Fiberglass Insulating Tubing for High-Temp Applications, 0.5 Inches (12.7 mm) Nominal Inside Diameter, 100 Feet (30.5 Meters) Reel. The reflective aluminized high-temp resistant fiberglass tubing is resistant to temperatures up to 1,200 F° (649 C°) and allows for use with irregular shapes. The tubing provides continuous abrasion resistance for wires, cables and tubing.

Specifications

Material	Insulated Fiberglass
Color	Silver
Resistance Properties	Abrasion-Resistant
Maximum Operating Temperature (°C)	649
Maximum Operating Temperature (°F)	1200
Nominal Diameter (In.)	0.5
Nominal Diameter (mm)	12.7
Overall Length (ft.)	100
Overall Length (m)	30.5
Product Type	Fiberglass Insulated Tubing

Packaging Detail

UPC	61305682676
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0779
Std. Ctn. Qty.	4
Std. Ctn. Volume (cf)	0.3115