

## Electronic dial gauge

MarCator 1086 Ri



### Application:

For static measurements of lengths and length differences

### Execution:

- Factor adjustable
- Large and high-contrast LCD display
- Digit height 11 mm
- With Integrated Wireless
- Permissible deviation MPEp for increment 0.0005=2 µm, for increment 0.01=20 µm
- mm/inch changeover

### Advantage:

- LOCK function (key lock)

### Delivery:

In case with CR 2450 battery



<b>Art. no.</b>	<b>33166 860</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4337627
<b>Length measuring range</b>	100 mm
<b>Digit increment</b>	0.0005 mm
<b>Min./max. measurement force</b>	1.6-3.5 N
<b>Error limit</b>	8 µm
<b>Repeat accuracy</b>	2 µm
<b>Data transmission type</b>	multiCOM/MarConnect
<b>IP protection class</b>	IP 42
<b>Absolute function</b>	Yes
<b>Automatic switch-off</b>	Yes
<b>Preset function</b>	Yes
<b>Tolerance value entry</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Rechargeable battery/battery capacity</b>	540 mAh
<b>Battery voltage</b>	3 V
<b>Weight of rechargeable battery/battery</b>	0.0059 kg
<b>Battery designation</b>	3V CR2450N lithium
<b>Rotating housing</b>	Yes
<b>Reversible counting direction</b>	Yes
<b>Calibration Group Description</b>	Dial gauge
<b>Calibration Group</b>	CE
<b>Gross Weight</b>	0.500 kg
<b>Product Group</b>	305

### EAN

4059192014568