

## LED workplace light Floodlight

With and without dimmer



### Execution:

- LED light, with flexible light arm, rubber-coated
- Low power consumption and low heat generation
- Solid and robust design for heavy-duty use
- High-performance chip with lamp life of min. 50,000 operating hours
- Anti-glare and flicker-free light, low reflection, with 24 V power supply
- Luminous flux: 1200 lumen, colour temperature: daylight white, approx. 5500 Kelvin, 160 degree uniform illumination
- 88-mm magnetic base with 420 N adhesive force
- Total length 850 mm, light head 175 x 50 x 25 mm
- Ref. no. 160: No dimmer
- Ref. no. 162: With dimmer (continuously variable)

### Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



<b>Art. no.</b>	<b>56879 162</b>
<b>Brand</b>	BAUER & BÖCKER
<b>Manufacturer Part Number</b>	900/43D
<b>Power rating</b>	10 W
<b>Arm length</b>	701 mm
<b>IP protection class</b>	IP 65
<b>Dimmable</b>	Yes
<b>Gross Weight</b>	1.500 kg
<b>Product Group</b>	5ID

### EAN

4260131238079