


- Plug-in unit
- Fixed output voltages
- Thermal fuse in transformer
- Can upon request be modified to comply with the standard for electromedical equipment (EN 60601)
- Exchangeable DC plugs
- Plugg-inn enhet
- Faste utgangsspenninger
- Termosikring i transformator
- Kan på forespørsel modifiseres til å tilfredstille medisinsk standard (EN 60601)
- Utskiftbare DC plugger



### Technical specifications

Input voltage:  
Output voltage:  
Max output power:  
Insulation class:  
Electrical safety standard:  
EMC standards

- Emission:
- Immunity:


Output terminals  
Cord with/without plug:  
Dimensions excl. plug (LxWxH):  
Weight:

### Tekniske data

Inngangsspenning: 230 VAC +6/-10%, 50/60Hz  
Utgangsspenning: 3-42 VAC  
Maks. utgangseffekt: 15,0 VA  
Isolasjonsklasse: II  
Elektrisk sikkerhetsstandard: EN 60065, EN 60742, EN 60950  
EMC standarder

- Emisjon: EN 61000-6-3
- Immunitet: EN 61000-6-1

Utgangsterminaler  
Sek. ledning med/uten plugg: Accessories /Tilbehør  
Mål uten plugg (LxBxH): 100 x 51 x 63 mm  
Vekt: 450 g



Voltage version (VAC) Spenningsversjoner (VAC)	Nominal load (mA) Merkelast (mA)
3	4000
4,5	3200
6	2300
7,5	2000
9	1600
10,5	1400
12	1100
15	1000
18	800
21	700
24	500
28	490
42	330

Max. load (A): See diagram  
Maks. last (A): Se kurve