

## Coaxial Cable Connector 11\_N-75-4-8/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	75 Ω
Interface frequency max.	1.5 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0295 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Catalogue drawing	DOU-00006925
Assembly instruction	DOC-0000179851

### Ordering Information

Single package	11_N-75-4-8/133_NE
----------------	--------------------

### Additional Information

Suitable cables	RG_59_B/U, GX_04273, GX_04273-12, G_04273-12
-----------------	--