

Model Number:	55-3213	
GENERAL SPECIFICATIONS		
Nominal Diameter:	15 inch	
Rated Impedance:	4 Ω	
Operating Bandwidth:	50 ~ 2.5KHz (-3dB)	
Power Handling Capacity:	200W RMS	
Sensitivity (1W/M):	98 dB(±3dB)	
Voice Coil Diameter:	3 inch	
THIELE-SMALL PARAMETERS		
Resonance Frequency	Fs:	32.49Hz
DC Resistance	Re:	3.4 Ω
Mechanical Q Factor	Qms:	3.0845
Electrical Q Factor	Qes:	0.5591
Total Q Factor	Qts:	0.4733
Equivalent Cas air load	Vas:	322.23 L
Surface Area of Cone	Sd:	0.084 m ²
Efficiency Bandwidth Product	EBP	58
Voice Coil Over Hang	X-max	6.0 mm
PHYSICAL INFORMATION		
Basket:	Pressed steel chassis	
Magnet Type:	67 Oz.	
Cone Material:	Non-pressed paper	
Surround:	cloth	
Dust Cap:	paper	
Damper:	cloth	

