

## Pneumatic drill 9030N-1

375 W



### Application:

Ideal for bodywork and industry

### Advantage:

- Suitable for continuous operation

### Delivery:

incl. coupling connector: Nominal width 7.2



<b>Art. no.</b>	<b>75032 211</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	9030N-1
<b>Model</b>	9030N-1
<b>Max. idle speed</b>	2000 rpm
<b>Power rating</b>	373 W
<b>Air consumption</b>	113 l/min
<b>Connection thread</b>	IT 1/4 inch
<b>Min./max. drill chuck span width</b>	1-10 mm
<b>Inner hose diameter</b>	10 mm
<b>Weight</b>	1 kg
<b>With right/left-hand rotation</b>	Yes
<b>Operating pressure</b>	6.3 bar
<b>Length</b>	195 mm
<b>Sound-pressure level</b>	88.7 dB
<b>Noise level</b>	96 dB
<b>Gross Weight</b>	1.267 kg
<b>Product Group</b>	738

### EAN

4000896206377