

L022790509

Navigation LED E27 T29x115mm 100-240V
1300Lm 10W 6500K 865 AC/DC IP65 EMC
approved Ship lamp

Marine & Industry, Navigation Led



General	
Eprel registration no	831194
Socket	E27
Bulb shape	T29
Width	29.00 mm
Depth	29.00 mm
Height	115.00 mm
Finish	Clear
Colour	White Daylight
Body material	Polycarbonat
Lifespan	25000 hours
Switches	50000
Beam angle	360 °
Dimmable	No
Degree of protection	IP65
Net weight	0.070 kg
Warranty	2 years

Energy	
Volt	100..240 V
Frequency	50..60 Hz
Watt	10 W
Current type	AC/DC
Power factor	0.5
Energy efficiency class	E
Energy consumption	10 W
Replacement wattage	88 W
Lamp efficacy	130.00

LED	
Filament LED	No
LED type	SMD
Dimm type	Non-Dim
Number of leds / sticks	72
Colour consistency SDCM	SDCM5
Dim to warm	No
Adjustable beam angle	No

Light	
Kelvin	6500 K
Colour temp nr	865
Stable lumen	1300 lm
Color Rendering Index (CRI)	80

Ordering details		
L022790509	Quantity pc(s)	EAN
Single package	1	8718739059641
Inner carton	10	18718739059648
Outer carton	100	28718739059645

