

Slides DZ 2109, Width 12.7 mm, with Bracket Mounts, to 35 kg, 3/4 Extension

Material:


Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Cold-rolled steel, zinc-plated.


Balls: Hardened steel.

Telescopic ball bearing slides, especially suited for keyboard trays.

- Fast disconnection.
- Hold-in in closed position and hold-out in open position.
- Height-adjustable bracket mount included.
- Optional clip-on bracket (page 630).
- Especially long service life, up to 50,000 cycles!
- Temperature range: -20°C to +70°C.




Ordering details: e.g.: Prod. No. 64906230, Slides DZ 2109, with Bracket Mounts



Product No. per Pair	Slide Length mm	Travel +/-3,2 mm	A mm	B mm	C mm	D mm	E mm	F* mm	Load Rating per pair kg	Weight per Pair kg
649 062 30	300	205	96	-	-	-	242	215,9	35	0,87
649 062 35	350	260	128	-	-	-	292	215,9	35	0,99
649 062 40	400	281	128	-	-	-	342	215,9	30	1,07
649 062 45	450	331	128	224	-	-	392	215,9	30	1,14
649 062 50	500	376	128	224	-	-	442	292,1	25	1,23
649 062 55	550	415	128	224	320	-	492	292,1	25	1,33

* See operating instructions on the internet at www.maedler.de in the Section Downloads.

Mounting Example: Sliding Keyboard Tray



Note

Recommended mount: M4 screw (included in delivery).

Use all mounting positions to achieve the max. load rating.

Clip-on brackets see page 630.

Selection Tool
on the Internet at www.maedler.de
in the section **MÄDLER®-Tools**