

Hydraulic short stroke cylinder RCS



Version:

- Single-acting cylinder
- Without fastening thread on cylinder head and piston rod
- Operating pressure of 700 bar
- With spring return and scraper ring
- Stripping ring
- Piston rod with nickel plating
- Model RCS 1002 with carry handle
- For RCS 101-502 models, the coupling sleeve is inserted at an angle of 5°.

Advantage:

- Retaining ring prevents piston rod from being pushed out

Delivery:

Pressure cylinder with CR400 coupler and fluted pressure fitting.



Art. no.	29511 050
Model	RCS 302
Max. compressive force	295 kN
Lift height	62 mm
Oil capacity	261 cm ³
Overall height, retracted	117 mm
Outer diameter	101 mm
Weight	6.8 kg