

180° counterbore, HSS, uncoated for medium through hole

for universal use up to 1,000 N/mm²

ORION[®]

Application:

For producing 180° counterbores of medium quality grade for through holes in accordance with DIN 74-2, type H, J, K and DIN 974-1.

Execution:

- profile-ground with spiral blade

Advantage:

- spiral chip flutes ensure smooth cutting and the blade does not catch



Art. no.	11449 100
Brand	ORION
Manufacturer Part Number	11449 100
Cutting material	HSS
Surface	Uncoated
Countersink angle	180 Degree
Tool holding device	HA parallel shank
Suitable for screw thread	M10
Spot-facer diameter	18 mm
Diameter of tenon	11 mm
Shank diameter	12.5 mm
Length	100 mm
DIN	373
Gross Weight	0.105 kg
Product Group	103

EAN

4039247036790