

TECHNICAL DATASHEET

Update : 25/02/2019

CYLINDRICAL DRILL BIT - HSS



Description

An N type drill bit for most common uses



Characteristics

Ref.	EAN	Drilling diameter mm	Total length mm	Length of cut mm	Body material	Sharpening	Tip angle	Tail diameter mm	Internal cooling	Din standard	Angle of helix °
845744	3660338077821	1	34	12	HSS	Standard	118	1	No	338 N	30
845745	3660338077838	1,1	36	14	HSS	Standard	118	1,1	No	338 N	30
845746	3660338077845	1,2	38	16	HSS	Standard	118	1,2	No	338 N	30
845747	3660338077852	1,3	38	16	HSS	Standard	118	1,3	No	338 N	30
845748	3660338077869	1,4	40	18	HSS	Standard	118	1,4	No	338 N	30
845749	3660338077876	1,5	40	18	HSS	Standard	118	1,5	No	338 N	30
845750	3660338077883	1,6	43	20	HSS	Standard	118	1,6	No	338 N	30
845751	3660338077890	1,7	43	20	HSS	Standard	118	1,7	No	338 N	30
845752	3660338077906	1,8	46	22	HSS	Standard	118	1,8	No	338 N	30
845753	3660338077913	1,9	46	22	HSS	Standard	118	1,9	No	338 N	30
845754	3660338077920	2	49	24	HSS	Standard	118	2	No	338 N	30
845755	3660338077937	2,1	49	24	HSS	Standard	118	2,1	No	338 N	30
845756	3660338077944	2,2	53	27	HSS	Standard	118	2,2	No	338 N	30
845757	3660338077951	2,3	53	27	HSS	Standard	118	2,3	No	338 N	30
845758	3660338077968	2,4	57	30	HSS	Standard	118	2,4	No	338 N	30
845759	3660338077975	2,5	57	30	HSS	Standard	118	2,5	No	338 N	30
845760	3660338077982	2,6	57	30	HSS	Standard	118	2,6	No	338 N	30
845761	3660338077999	2,7	61	33	HSS	Standard	118	2,7	No	338 N	30
845762	3660338078002	2,8	61	33	HSS	Standard	118	2,8	No	338 N	30
845763	3660338078019	2,9	61	33	HSS	Standard	118	2,9	No	338 N	30
845764	3660338078026	3	61	33	HSS	Standard	118	3	No	338 N	30
845767	3660338078057	3,1	65	36	HSS	Standard	118	3,1	No	338 N	30
845765	3660338078033	3,2	65	36	HSS	Standard	118	3,2	No	338 N	30
845766	3660338078040	3,3	65	36	HSS	Standard	118	3,3	No	338 N	30
845768	3660338078064	3,4	70	39	HSS	Standard	118	3,4	No	338 N	30
845769	3660338078071	3,5	70	39	HSS	Standard	118	3,5	No	338 N	30
845770	3660338078088	3,6	70	39	HSS	Standard	118	3,6	No	338 N	30
845771	3660338078095	3,7	70	39	HSS	Standard	118	3,7	No	338 N	30
845772	3660338078101	3,8	75	43	HSS	Standard	118	3,8	No	338 N	30
845773	3660338078118	3,9	75	43	HSS	Standard	118	3,9	No	338 N	30
845774	3660338078125	4	75	43	HSS	Standard	118	4	No	338 N	30
845775	3660338078132	4,1	75	43	HSS	Standard	118	4,1	No	338 N	30
845776	3660338078149	4,2	75	43	HSS	Standard	118	4,2	No	338 N	30
845777	3660338078156	4,3	80	47	HSS	Standard	118	4,3	No	338 N	30
845778	3660338078163	4,4	80	47	HSS	Standard	118	4,4	No	338 N	30
845779	3660338078170	4,5	80	47	HSS	Standard	118	4,5	No	338 N	30
845780	3660338078187	4,6	80	47	HSS	Standard	118	4,6	No	338 N	30

845781	3660338078194	4,7	80	47	HSS	Standard	118	4,7	No	338 N	30
845782	3660338078200	4,8	86	52	HSS	Standard	118	4,8	No	338 N	30
845783	3660338078217	4,9	86	52	HSS	Standard	118	4,9	No	338 N	30
845784	3660338078224	5	86	52	HSS	Standard	118	5	No	338 N	30
845785	3660338078231	5,1	86	52	HSS	Standard	118	5,1	No	338 N	30
845786	3660338078248	5,2	86	52	HSS	Standard	118	5,2	No	338 N	30
845787	3660338078255	5,3	86	52	HSS	Standard	118	5,3	No	338 N	30
845788	3660338078262	5,4	93	57	HSS	Standard	118	5,4	No	338 N	30
845789	3660338078279	5,5	93	57	HSS	Standard	118	5,5	No	338 N	30
845790	3660338078286	5,6	93	57	HSS	Standard	118	5,6	No	338 N	30
845791	3660338078293	5,7	93	57	HSS	Standard	118	5,7	No	338 N	30
845792	3660338078309	5,8	93	57	HSS	Standard	118	5,8	No	338 N	30
845793	3660338078316	5,9	93	57	HSS	Standard	118	5,9	No	338 N	30
845794	3660338078323	6	93	57	HSS	Standard	118	6	No	338 N	30
845795	3660338078330	6,1	101	63	HSS	Standard	118	6,1	No	338 N	30
845796	3660338078347	6,2	101	63	HSS	Standard	118	6,2	No	338 N	30
845797	3660338078354	6,3	101	63	HSS	Standard	118	6,3	No	338 N	30
845798	3660338078361	6,4	101	63	HSS	Standard	118	6,4	No	338 N	30
845799	3660338078378	6,5	101	63	HSS	Standard	118	6,5	No	338 N	30
845800	3660338078385	6,6	101	63	HSS	Standard	118	6,6	No	338 N	30
845801	3660338078392	6,7	101	63	HSS	Standard	118	6,7	No	338 N	30
845802	3660338078408	6,8	109	69	HSS	Standard	118	6,8	No	338 N	30
845803	3660338078415	6,9	109	69	HSS	Standard	118	6,9	No	338 N	30
845804	3660338078422	7	109	69	HSS	Standard	118	7	No	338 N	30
845805	3660338078439	7,1	109	69	HSS	Standard	118	7,1	No	338 N	30
845806	3660338078446	7,2	109	69	HSS	Standard	118	7,2	No	338 N	30
845807	3660338078453	7,3	109	69	HSS	Standard	118	7,3	No	338 N	30
845808	3660338078460	7,4	109	69	HSS	Standard	118	7,4	No	338 N	30
845809	3660338078477	7,5	109	69	HSS	Standard	118	7,5	No	338 N	30
845810	3660338078484	7,6	117	75	HSS	Standard	118	7,6	No	338 N	30
845811	3660338078491	7,7	117	75	HSS	Standard	118	7,7	No	338 N	30
845812	3660338078507	7,8	117	75	HSS	Standard	118	7,8	No	338 N	30
845813	3660338078514	7,9	117	75	HSS	Standard	118	7,9	No	338 N	30
845814	3660338078521	8	117	75	HSS	Standard	118	8	No	338 N	30
845815	3660338078538	8,1	117	75	HSS	Standard	118	8,1	No	338 N	30
845816	3660338078545	8,2	117	75	HSS	Standard	118	8,2	No	338 N	30
845817	3660338078552	8,3	117	75	HSS	Standard	118	8,3	No	338 N	30
845818	3660338078569	8,4	117	75	HSS	Standard	118	8,4	No	338 N	30
845819	3660338078576	8,5	117	75	HSS	Standard	118	8,5	No	338 N	30
845820	3660338078583	8,6	125	81	HSS	Standard	118	8,6	No	338 N	30
845821	3660338078590	8,7	125	81	HSS	Standard	118	8,7	No	338 N	30
845822	3660338078606	8,8	125	81	HSS	Standard	118	8,8	No	338 N	30
845823	3660338078613	8,9	125	81	HSS	Standard	118	8,9	No	338 N	30
845824	3660338078620	9	125	81	HSS	Standard	118	9	No	338 N	30
845825	3660338078637	9,1	125	81	HSS	Standard	118	9,1	No	338 N	30
845826	3660338078644	9,2	125	81	HSS	Standard	118	9,2	No	338 N	30
845827	3660338078651	9,3	125	81	HSS	Standard	118	9,3	No	338 N	30
845828	3660338078668	9,4	125	81	HSS	Standard	118	9,4	No	338 N	30
845829	3660338078675	9,5	125	81	HSS	Standard	118	9,5	No	338 N	30
845830	3660338078682	9,6	133	87	HSS	Standard	118	9,6	No	338 N	30
845831	3660338078699	9,7	133	87	HSS	Standard	118	9,7	No	338 N	30
845832	3660338078705	9,8	133	87	HSS	Standard	118	9,8	No	338 N	30
845833	3660338078712	9,9	133	87	HSS	Standard	118	9,9	No	338 N	30
845834	3660338078729	10	133	87	HSS	Standard	118	10	No	338 N	30
845835	3660338078736	10,1	133	87	HSS	Standard	118	10,1	No	338 N	30
845836	3660338078743	10,2	133	87	HSS	Standard	118	10,2	No	338 N	30
845837	3660338078750	10,3	133	87	HSS	Standard	118	10,3	No	338 N	30
845838	3660338078767	10,4	133	87	HSS	Standard	118	10,4	No	338 N	30
845839	3660338078774	10,5	133	87	HSS	Standard	118	10,5	No	338 N	30
845840	3660338078781	11	142	94	HSS	Standard	118	11	No	338 N	30
845841	3660338078798	11,5	142	94	HSS	Standard	118	11,5	No	338 N	30
845842	3660338078804	12	151	101	HSS	Standard	118	12	No	338 N	30
845843	3660338078811	12,5	151	101	HSS	Standard	118	12,5	No	338 N	30
845844	3660338078828	13	151	101	HSS	Standard	118	13	No	338 N	30