

16927128. - verso maintenance trolley


Short Description

verso maintenance trolley with 7 drawers, door and top tray

WxDxH: 1050x550x965mm

Product Images





Description	verso maintenance trolley with 7 drawers / cupboard & top tray with mat. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 6x 100mm, 1x 125mm (50kg U.D.L.) and cupboard section with single, reinforced, door and 1 galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint. WxDxH: 1050x550x965mm
Width	1050
Depth	550
Height	965
Customs tariff number	94032080
Product material	Sheet steel
Product surface	Powder coated
Drawer Load Capacity	50 kg
Drawer height 1	100mm
Drawer 1 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 2	100mm
Drawer 2 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 3	100mm
Drawer 3 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 4	100mm
Drawer 4 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 5	100mm
Drawer 5 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 6	100mm
Drawer 6 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 7	125mm
Additional Information Drawer 7 Internal Dimensions	930mm x 430mm x 100mm
Door type	Plain

Door height 1	675 mm
Number of shelves	1
Shelf Material	Steel
Shelf Load Capacity	75kg

Product Options

Colour:	Anthracite grey
	Crimson red
	Gentian blue
	Light grey