

ROLINE DesignSecure 825

Product No.	19.40.1208
Manufacturer	ROLINE
Manufacturer No.	19.40.1208
EAN (single piece)	7611990171033



- Compact designed UPS in futuristic design
- For Workstations and PCs
- LineInteractive UPS
- AVR (Automatic Voltage Regulation)
- Digital status display
- Integrated overvoltage protection
- Telephone/Modem connections
- USB Port for advanced Power Management Software (incl, in content of delivery)
- EMI/RFI Noise Filter
- Dimensions (HxLxW) 168 x 105 x 334 mm
- Weight: 6.3 kg
- Backup Time: up to 4 Minutes

Technical specifications	
Manufacturer	ROLINE
Product group	UPS
Product type	UPS Line Interactive
Colour	black /silver
Scope of delivery	UPS, Software, Cable Set
Classification (IEC 62040-3)	VI-SS-333

UPS technology	Line Interactive
Power class	600 ... 900 VA
Output (VA/W)	825/495
Backup time	2 min
Backup time full/half-load	2 / 4 min
Weight	6,3 kg
Dimensions (HxWxD)	168 x 105 x 334 mm
Mounting form	Turm
Voltage (input)	230 V
Voltage (output)	230 V
Output voltage regulation	Ja
Frequency	50 Hz
Connector type (input)	Kaltgeräte IEC320 C14
Outputs	5
Connector type (output)	2x 3 Kaltgeräte IEC320 C13
Phase in/output	230V/230V / 50Hz
Over current protection	EMI,- RFI-Filter
Max. quantity of delay expansion units	0
Delay expansion unit	--
Slots for adapter card	0
Slot for adapter card	--
Interface	USB
USB 2.0 Interface	Yes
Hot swap batteries	No
Bypass	No
Additional over current protector	Telephone/Fax
Activity	Display

Activity LED	--
Activity Display	ja
incl.Management Software	Windows
Internal cooling	Passive
Ambient temperature	0-40 °C

Backup Time	
Capacity (VA / W)	minutes
100	53
200	24
300	11
425	7
525	4
625	3
725	2,5
825	2