# HellermannTyton

DF

Download spec sheet

## SNP1910C2

	Article Number: 190-00094
2	Snapper Hose Clamps, .884"/.997" Min/Max Diameter, POM, White, 100/pkg
	ROHS

Download drawing
Base Data

Local Order Number	SNP1910C2
Туре	SNP19
Color	White (WH)
Features and Benefits	<ul> <li>Designed for quick, ratcheted installation and can be released and reused.</li> <li>Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.</li> </ul>
Product Description	HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.
Short Description	Snapper Hose Clamps, .884"/.997" Min/Max Diameter, POM, White, 100/pkg

#### **Product Dimensions**

Fixation Method	Plug-in mounting
Variant	Closed
Width W2 (Imperial)	0.228 "
Width W2 (Metric)	5.79 mm
Diameter Min. (Imperial)	0.884 "
Diameter Min. (Metric)	22.45 mm
Diameter Max. (Imperial)	0.997 "
Diameter Max. (Metric)	25.32 mm
Wall Thickness WT (Imperial)	0.07 "
Wall Thickness WT (Metric)	1.8 mm

### Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100
Carton Quantity	2000

#### **Material and Specifications**

Material	Polyacetal (POM)
Material Shortcut	POM
Flammability	UL94 HB
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
<b>ROHS</b> Compliant	Yes

© HellermannTyton 2015