


P2662B

Pylon Probe

Product Family: Pylon



Mechanical:

Test Center (mil): 50

Test Center (mm): 1.27

Overall Length (mil): 575

Overall Length (mm): 14.60

Full Travel (mil): 68

Full Travel (mm): 1.73

Recommended Travel (mil): 50

Recommended Travel (mm): 1.27

Thermal:

Max Operating Temp (°C): 85

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 3

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over hard Nickel

Barrel Material: Phosphor Bronze, Gold plated

Ball Material: Stainless Steel

Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 1.00 (28.00) - 1.80 (51.00) - BeCu, Silver plated

Alternate - 0.50 (14.00) - 2.50 (71.00) - BeCu, Silver plated

Body Type

Straight

Pylon Bend

Additional information:


Use tool RIT-0-0 for installation

TIPS:


Tip Materials: BeCu, Gold plated

Tips:

P2662-1C




P2662-1Q



P2662-1R




P2662-2V




Related Products:


PR261-0




PR261-0F



PR261-1



PR261-1F



RIT-0-0

