


20836-415 VMEBUS SYSTEM, 4 U, 8 SLOT, OPEN FRAME PSU



KEY FEATURES

System in accordance with IEC-60297-3-101, -102, -103; IEEE-1101.1, 1101.10/11; Backplane-conforms to VITA 1.1-1994

PSU, open frame, 444 W (400-W at <-180 VAC)

Backplane VME 8-slot, 6-U, J1/J2 monolithic in accordance with VITA 1-1994

Heat dissipation by 2 fans, cooling from front to left side; temperature-controlled with fan control module (FCM)

Display module for DC operating voltages, fan and temperature alarm

PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 8

Type: 19" Rack Mount

Backplane Type: 6 U VME64

Data Transfer: VME64; VME2eSST

Power per Slot: 30 W

Input Voltage AC: 100 – 240 V

Airflow Direction: Front to Left

Rack Height: 4 U

Power Supply Type: Open Frame

Power Supply Included: Yes

Rear I/O: No

Complies With: ANSI/VITA 1.1-1994

Depth: 277.5 mm

Height: 177 mm

Width: 449 mm

Power: 350 W

ADDITIONAL PRODUCT DETAILS

VME system for 8 horizontally mounted VME boards 6 U, 160 mm. The power for the system is supplied by an open frame power supply. A fan control module monitors the fans, the temperature and voltage.

Modified systems available on request.

CERTIFICATIONS



North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.