


### Tubular Handles 333, with Inclined Feet, Aluminium

**Material:** Grip tube Ø28mm x 1.5 mm made from Aluminium. Either natural coloured anodised or black plastic coated RAL 9005 matt.  
Feet made from zinc die cast, black plastic coated RAL 9005 matt.  
High stability for small sizes. Tube either aluminium silver or black. Grip tube fixed against turning with screws on the face ends (screws below bright grey removable plastic caps).  
**Other sizes on request.**




Ordering Details: e.g.: Product No. 666 505 02, Tubular handle 333, aluminium colour, length 200mm

| Product No.<br>alu colour | Product No.<br>black | $l_1^{+0,5}$<br>mm | $d_1$<br>mm | $d_2$<br>mm | $b_1$<br>mm | $b_2$<br>mm | $b_3$<br>mm | $h_1$<br>mm | $h_2$<br>mm | $l_2$<br>mm | $l_3$<br>mm | $t_{min.}$<br>mm | Weight<br>g |
|---------------------------|----------------------|--------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|------------------|-------------|
| 666 505 02                | 666 505 22           | 200                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 214         | 186         | 15               | 432         |
| 666 505 04                | 666 505 24           | 250                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 264         | 236         | 15               | 455         |
| 666 505 06                | 666 505 26           | 300                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 314         | 286         | 15               | 470         |
| 666 505 08                | 666 505 28           | 400                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 414         | 386         | 15               | 530         |
| 666 505 10                | 666 505 30           | 500                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 514         | 486         | 15               | 575         |
| 666 505 12                | 666 505 32           | 600                | 28          | M8          | 50          | 66          | 25          | 50          | 66          | 614         | 586         | 15               | 620         |

### Tubular Handles 333.1, with Straight Feet, Aluminium

**Material:** Grip tube Ø20mm / Ø28mm x 1.5mm made from Aluminium. Either natural coloured anodised or black plastic coated RAL 9005 matt.  
Feet made from zinc die cast, black plastic coated RAL 9005 matt.  
High stability for small sizes. Tube either aluminium silver or black. Grip tube fixed against turning with screws on the face ends (screws below bright grey removable plastic caps).  
**Other sizes on request.**



Ordering Details: e.g.: Product No. 666 505 02, Tubular handle 333.1, aluminium colour, length 180mm


| Product No.<br>alu colour | Product No.<br>black | $l_1^{+0,2}$<br>mm | $d_1$<br>mm | $d_2$<br>mm | $b$<br>mm | $h_1$<br>mm | $h_2$<br>mm | $l_2$<br>mm | $l_3$<br>mm | $t_{min.}$<br>mm | Weight<br>g |
|---------------------------|----------------------|--------------------|-------------|-------------|-----------|-------------|-------------|-------------|-------------|------------------|-------------|
| 666 505 42                | 666 505 72           | 180                | 20          | M6          | 24        | 42          | 54          | 192         | 168         | 12               | 190         |
| 666 505 44                | 666 505 74           | 200                | 20          | M6          | 24        | 42          | 54          | 212         | 188         | 12               | 200         |
| 666 505 46                | 666 505 76           | 250                | 20          | M6          | 24        | 42          | 54          | 262         | 238         | 12               | 225         |
| 666 505 48                | 666 505 78           | 300                | 20          | M6          | 24        | 42          | 54          | 312         | 288         | 12               | 250         |
| 666 505 50                | 666 505 80           | 400                | 20          | M6          | 24        | 42          | 54          | 412         | 388         | 12               | 300         |
| 666 505 52                | 666 505 82           | 200                | 28          | M8          | 25        | 50          | 66          | 214         | 186         | 15               | 340         |
| 666 505 54                | 666 505 84           | 250                | 28          | M8          | 25        | 50          | 66          | 264         | 236         | 15               | 360         |
| 666 505 56                | 666 505 86           | 300                | 28          | M8          | 25        | 50          | 66          | 314         | 286         | 15               | 380         |
| 666 505 58                | 666 505 88           | 400                | 28          | M8          | 25        | 50          | 66          | 414         | 386         | 15               | 440         |
| 666 505 60                | 666 505 90           | 500                | 28          | M8          | 25        | 50          | 66          | 514         | 486         | 15               | 480         |
| 666 505 62                | 666 505 92           | 600                | 28          | M8          | 25        | 50          | 66          | 614         | 586         | 15               | 520         |

### Tubular Handles 335, with Straight Feet, Stainless Steel

**Material:** Grip tube Ø28mm x 2 mm made from Stainless Steel 1.4305 (AISI 303), silk matt gloss, ground. **STAINLESS**  
Feet made from stainless steel, precision cast 1.4308 (CF-8), matt blasted.

Very high stability for small sizes.  
Connection between tube and foot is sealed against water spray.

**Other sizes on request.**



Ordering Details: e.g.: Product No. 666 995 52, Tubular handle 335, length 200 mm

| Product No.<br>stainless | $l_1^{+1}$<br>mm | $d_1$<br>mm | $d_2$<br>mm | $b$<br>mm | $h_1$<br>mm | $h_2$<br>mm | $l_2$<br>mm | $l_3$<br>mm | $t_{min.}$<br>mm | Weight<br>g |
|--------------------------|------------------|-------------|-------------|-----------|-------------|-------------|-------------|-------------|------------------|-------------|
| 666 995 52               | 200              | 28          | M8          | 25        | 50          | 66          | 214         | 186         | 15               | 500         |
| 666 995 54               | 250              | 28          | M8          | 25        | 50          | 66          | 264         | 236         | 15               | 565         |
| 666 995 56               | 300              | 28          | M8          | 25        | 50          | 66          | 314         | 286         | 15               | 630         |
| 666 995 58               | 400              | 28          | M8          | 25        | 50          | 66          | 414         | 386         | 15               | 760         |
| 666 995 60               | 500              | 28          | M8          | 25        | 50          | 66          | 514         | 486         | 15               | 890         |
| 666 995 62               | 600              | 28          | M8          | 25        | 50          | 66          | 614         | 586         | 15               | 1020        |