

## Clamping screw sets



### Execution:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

### Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



<b>Art. no.</b>	<b>26209 220</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	83055
<b>Suitable for groove width</b>	22 mm
<b>Thread dimension</b>	M20
<b>Number of DIN 787 T-slot screws</b>	2 x M20 x 80 mm, 4 x M20 x 125 mm
<b>Number of DIN 6379 stud bolts (extension pin)</b>	4 x M20 x 80 mm, 4 x M20 x 125 mm, 4 x M20 x 200 mm, 4 x M20 x 315 mm
<b>Number of DIN 508 slots</b>	4 PCS
<b>Number of DIN 6330 B high nuts</b>	4 PCS
<b>Number of extension nuts</b>	4 PCS
<b>Wooden box length</b>	358 mm
<b>Wooden box width</b>	342 mm
<b>Wooden box height</b>	56 mm
<b>Gross Weight</b>	12.800 kg
<b>Product Group</b>	260

### EAN

4020772083052