





1000+30/-0mm



WIRE ADDRESS



Electrical Test:

1. 100% TEST OPEN SHORT MIS-WIRE.
2. CONTACT RESISTANCE:5Ω MAX.
3. INSULATION RESISTANCE:5MΩ MIN.
4. HI-POT:300V DC/10MS.
5. Real Test Passed 7860*3840 60HZ
6. Real Test Not Twinking, Double Vision and Decolor.

C	45P BLACK PVC	G
B	1 Z-11.04.5940	2 PCS
A	UL20276 (30AWG*1P+DAM)*5+30AWG*4C+ADB,OD:6.0mm BLACK COLOR PVC JACKET (CABLE PRINTING:High Speed HDMI™ Cable with Ethernet)	1 PCS
NUMBER	BOM.NO	PRODUCT SPECIFICATIONS

Item	11.04.5940
Draw	Shake Date: 2018.10.18
Approval	
Duty	F16 BOM.NO:
Company: RLA	REVERSE
VER.A	DATE

