



STRIPPER,KWIK (34-10 AWG).

Kwik Stripper Wire Stripper

Cat No: 45000

UPC No: 783310450009

Description

- 34 - 10 AWG (0.08 - 6 MM²) stripping capacity
- 12 AWG (4 MM²) solid, 10 AWG (6 MM²) stranded capacity
- Strips and cuts flat and round cable
- Self-adjusts to different wire gauges
- Laminated steel blades minimize the risk of nicking conductors
- Front entry jaws have an adjustable strip length guide
- Lightweight reinforced nylon is chemical and corrosion resistant
- Note: This is not an insulated tool

Specifications

- Application : Strips And Cuts Flat And Round Cable
- Capacity : 34-10 AWG (0.080 - 6.000 MM²), 12 AWG (4 MM²) Solid, 10 AWG(6 MM²) Stranded
- Handle Type : Lightweight Reinforced Nylon
- Material : Steel Blade
- Replacement Part : 20243 Blade Cassette
- Sub Brand : Kwik Stripper