

Electronic dial gauge

MarCator 1087 Ri



Application:

For static and dynamic measurements of lengths and length differences, e.g. concentricity, flatness, position measurements.

Execution:

- Factor adjustable
- mm/inch changeover
- LOCK function (key lock)
- With integrated wireless transmission
- Permissible deviation MPEp 2 µm

Delivery:

In case with CR 2450 battery



Art. no.	33166 695
Brand	MAHR
Manufacturer Part Number	4337667
Length measuring range	50 mm
Digit increment	0.0005 mm
Min./max. measurement force	0.65-1.1 N
Error limit	8 µm
Repeat accuracy	1 µm
Data transmission type	multiCOM/MarConnect
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Dynamic measurement	Yes
Preset function	Yes
Tolerance value entry	Yes
Number of rechargeable batteries/batteries	1 PCS
Rechargeable battery/battery capacity	540 mAh
Battery voltage	3 V
Weight of rechargeable battery/battery	0.0059 kg
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Combined indicator for figure/scale reading	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.360 kg
Product Group	305

EAN

4059192061456