

Slides DP 9301 E, Corrosion Proof, Width 19.1 mm, to 272 kg, Full Extension

Material: Slide elements: Cold-rolled steel, bright zinc-plated, with organic-mineral coating for high corrosion resistance.
Ball retainers: Plastic. Balls: Stainless steel.

Telescopic ball bearing slides for applications in the industrial and electronics sector.


- Slides sold separately (singly, not by pair).
- Good corrosion resistance.
- Lubricated with grease for food.
- Service life 10,000 cycles.
- Temperature range: -20°C to +70°C.

Note: Sold singly.



Accuride

Ordering details: e.g.: Prod. No. 649 057 10, 1 piece Slide DP 9301 E



Product-No. per Piece	Slide Length mm	Travel +/-3,3 mm	A	B	C	D	E	F	G	H	J	K	M	N	P	Q	R	Load Rating per Pair kg	Weight Piece kg
649 057 10	254	254	-	-	-	-	-	103,1	128,5	147,6	166,6	-	-	-	152,4	209,6	228,6	272	1,15
649 057 12	305	305	-	-	-	-	-	153,9	179,3	198,4	217,4	-	-	-	203,2	260,4	279,4	272	1,40
649 057 14	356	356	-	-	-	-	-	204,7	230,1	249,2	268,2	-	-	-	254,0	311,2	330,2	272	1,64
649 057 16	406	406	127	-	-	-	-	255,5	280,9	300,0	319,0	-	-	-	304,8	362,0	381,0	272	1,90
649 057 18	457	457	127	-	-	-	246,1	306,3	331,7	350,8	369,8	-	-	-	355,6	412,8	431,8	272	2,15
649 057 20	508	508	127	190,5	-	-	296,9	357,1	382,5	401,6	420,6	-	-	-	406,4	463,6	482,6	272	2,38
649 057 22	559	559	127	190,5	-	-	347,7	407,9	433,3	452,4	471,4	-	-	-	457,2	514,4	533,4	272	2,61
649 057 24	610	610	127	190,5	-	-	398,5	458,7	484,1	503,2	522,2	-	-	-	508,0	565,2	584,2	267	2,88
649 057 26	660	660	127	190,5	-	-	449,3	509,5	534,9	554,0	573,0	-	-	-	558,8	616,0	635,0	264	3,13
649 057 28	711	711	127	190,5	-	-	500,1	560,3	585,7	604,8	623,8	-	-	-	609,6	666,8	685,8	261	3,37
649 057 30	762	762	127	190,5	368,3	-	550,9	611,1	636,5	655,6	674,6	235	-	501,7	660,4	717,6	736,6	258	3,62
649 057 32	813	813	127	190,5	368,3	-	601,7	661,9	687,3	706,4	725,4	235	393,7	552,5	711,2	768,4	787,4	256	3,86
649 057 34	864	864	127	190,5	368,3	469,9	652,5	712,7	738,1	757,2	776,2	235	419,1	603,3	762,0	819,2	838,2	253	4,15
649 057 36	914	914	127	190,5	368,3	520,7	703,3	763,5	788,9	808,0	827,0	235	444,5	654,1	812,8	870,0	889,0	248	4,37
649 057 40	1016	1016	127	190,5	368,3	520,7	804,9	865,1	890,5	909,6	928,6	235	546,1	755,7	914,4	971,6	990,6	237	4,88
649 057 42	1067	1067	127	190,5	368,3	520,7	855,7	915,9	941,3	960,4	979,4	235	546,1	806,5	965,2	1022,4	1041,4	228	5,11
649 057 44	1118	1118	127	190,5	368,3	520,7	906,5	966,7	992,1	1011,2	1030,2	235	546,1	857,3	1016,0	1073,2	1092,2	218	5,35
649 057 48	1219	1219	127	190,5	368,3	520,7	1008,1	1068,3	1093,7	1112,8	1131,8	235	596,9	958,9	1117,8	1174,8	1193,8	204	5,86

Note

Recommended mount: M5/M6 screw. Max. screw head of 4.8 mm height and 12.7 mm Ø.
Use all mounting positions to achieve the max. load rating.

For horizontally (flat) mounted slides the load bearing capacity is reduced to only 25% of the stated load rating.